Better chemistry. Better business.

Hubbard-Hall Inc. • 563 South Leonard Street, Waterbury, CT 07608 • HubbardHall.com • 800-648-3412

Product Bulletin

Product Name: Resist Stripper 17 Product Code: 2702001 Revision Date: June 26, 2020

Resist Stripper 17

Resist Stripper 17 is an alkaline, water soluble liquid, which is added to water to remove aqueous and semi-aqueous dry film resists and alkaline soluble screen inks from circuit boards. It does contain a water-soluble glycol ether solvent.

Resist Stripper 17 is free of phenols, chromates, phosphates and silicones.

Resist Stripper 17 may be used by immersion (with or without air agitation) or in a pressure spray operation. While the stripping operation will not foam initially, a foam head may form after some resist is dissolved. Hubbard-Hall has several defoamers that are consistent with Resist Stripper 17.

Features & Benefits

Does not attack epoxy	Lower reject rate, higher productivity; lower process cost
Easy to control and	Lower labor cost
operate	
No effect on hole wall	Reduces chance of rejects;
adhesion	higher productivity, lower cost

Operating Conditions

Concentration	10% – 25%
Temperature	25% optimum (71°C) lower
	limits recommended for spray
	or ultra-sonics.
Optimum temp. range	120°F – 140°F (49°C – 60°C)
	At temperatures over 125°F,
	the copper surface may begin
	to tarnish.
Equipment	Polyethylene, Polypropylene,
	PVC, or 316 stainless steel
	tank, risers or nozzles.
Heaters	Quartz or 316 stainless steel
	immersion heaters









Better chemistry. Better business.

Hubbard-Hall Inc. • 563 South Leonard Street, Waterbury, CT 07608 • HubbardHall.com • 800-648-3412

Product Bulletin

Product Name: Resist Stripper 17 Product Code: 2702001 Revision Date: June 26, 2020

Spray Operations

Resist Stripper 17 is a non-foaming product. However, there are several inks on the market that will cause foaming when dissolved in a resist stripper. If the foaming problem becomes serious, Hubbard-Hall recommends Defoamer RS.

Titration Method

- 1. Pipette a 5 mL sample of Resist Stripper 17 into a 250 mL Erlenmeyer flask.
- 2. Add about 50 mL of water and several drops of Bromophenol Blue indicator.
- 3. Titrate with 0.5 N Hydrochloric Acid solution until the color changes from blue to light green.
- 4. Record mL used.

Calculation

Concentration = mL 0.5 N HCl x 1.48

Waste Disposal

Neutralize solutions of Resist Stripper 17 to a pH between 6.0 to 8.0 with a dilute mineral acid. Use caution when adding the acid since neutralization generates heat. Discharge the neutralized solution to disposal area. In order to be completely informed on the latest disposal regulations for your area, please contact the local authorities. For the removal of dissolved particles of photoresist, Aquapure FA may be dosed to form a manageable precipitate.

Caution

Resist Stripper 17 is an alkaline product and should be handled accordingly. Avoid skin, eye and oral contact. Wear protective clothing, gloves and goggles. Flush exposed areas immediately with clean cold water. In case of injury contact a doctor immediately.









Better chemistry. Better business.

Hubbard-Hall Inc. • 563 South Leonard Street, Waterbury, CT 07608 • HubbardHall.com • 800-648-3412

Product Bulletin

Product Name: Resist Stripper 17 Product Code: 2702001 Revision Date: June 26, 2020

WARRANTY: THE QUALITY OF THIS PRODUCT IS GUARANTEED ON SHIPMENT FROM OUR PLANT. IF THE USE RECOMMENDATIONS ARE FOLLOWED, DESIRED RESULTS WILL BE OBTAINED. SINCE THE USE OF OUR PRODUCTS IS BEYOND OUR CONTROL, NO GUARANTEE EXPRESSED OR IMPLIED IS MADE AS TO THE EFFECTS OF SUCH USE, OR THE RESULTS TO BE OBTAINED.

Our people. Your problem solvers.

For more information on this process please call us at 1-800-648-3412

or techservice@hubbardhall.com











